





ASM 390, universal voltage, configurable I/O interface board, outlet DN 25 ISO-KF








## ASM 390, universal voltage, configurable I/O interface board, outlet DN 25 ISO-KF

- Dry and clean pump with high backing pump capacity (35 m<sup>3</sup>/h)
- Minimum test time: unrivalled performance on small and large specimens
- Slim design and high maneuverability
- Large color touch screen, fully rotatable and detachable without any tool
- Integrated toolbox for storing accessories
- Fully configurable I/O interface (37 pins D-Sub) for control via PCs/PLCs
- Connectable DN 25 exhaust for connection to a general Fab exhaust

## **Dimensions**




Technical Data	ASM 390, universal voltage, configurable I/O interface board, outlet DN 25 ISO-KF
Pumping speed backing pump	35 m³/h
Pumping speed for He	10 l/s
Test method	Vacuum leak detection   Sniffing leak detection
I/O interfaces	RS232, USB
Interface: Connection, device side	Configurable 37 pins I/O
Туре	High performance - mobile
Minimum detectable leakage rate for helium (vacuum leak detection)	1 · 10 <sup>-13</sup> Pa m³/s
User interface	Graphic color touch screen (detachable)
Backing pump capacity	35 m³/h
Operating temperature	10 – 35 °C
Start-up time (20°C)	2 min
Exhaust connection	DN 25 ISO-KF
Input voltage(s)	100 – 240 V AC, 50/60 Hz
Emission sound pressure level (EN ISO 2151)	55 dB(A)
Start-up time (20°C)	2 min
Pumping speed for He	10 l/s
Minimum detectable leakage rate for helium (sniffing leak detection)	1 · 10 <sup>-9</sup> Pa m <sup>3</sup> 1.33 · 10 <sup>-7</sup> 1 · 10 <sup>-7</sup> /s   Torr l/s   mbar l/s
Weight	125 kg   275.58 lb
Detectable gases	$^{4}$ He   $^{3}$ He   H $_{2}$
Power consumption	800 W
Dimensions (L x W x H)	1072 x 455 x 1025 mm
Power consumption max.	1,600 W
Backing pump	With oil-free backing pump
Weight	125 kg
Connection flange (in)	DN 40 ISO-KF
Connection flange (out)	DN 25 ISO-KF

Order number	ASM 390, universal voltage, configurable I/C interface board, outlet DN 25 ISO-KF
ASM 390, universal voltage, configurable I/O interface board, outlet DN 25 ISO-KF	CSGB01G2MM9B



## Your Success. Our Passion.

We give our best for you every day worldwide!



Or scan the barcode, to visit our web page:



https://webportal.pfeiffer-vacuum.com/global/en/contact





Follow Us On Social Media #pfeiffervacuum













www.pfeiffer-vacuum.com

